

常用型号规格

快速交换型(RX型)    导丝适配:0.014"    公称压力:6atm

| 球囊尺寸                     | 鞘管匹配要求 |
|--------------------------|--------|
| 1.25mm×15mm—4.00mm×120mm | 4F     |
| 4.00mm×150mm—7.00mm×60mm | 5F     |

球囊额定爆破压



|             | 球囊长度 (mm) |            |            |            |            |            |            |            |
|-------------|-----------|------------|------------|------------|------------|------------|------------|------------|
|             | 球囊直径 (mm) | 15         | 20         | 30         | 40         | 60         | 80         | 100        |
| 输送杆长 80 cm  | 1.50      | K30-15015S | K30-15020S | K30-15030S | K30-15040S | K30-15060S | K30-15080S | K30-15100S |
|             | 2.00      | K30-20015S | K30-20020S | K30-20030S | K30-20040S | K30-20060S | K30-20080S | K30-20100S |
|             | 3.00      | K30-30015S | K30-30020S | K30-30030S | K30-30040S | K30-30060S | K30-30080S | K30-30100S |
|             | 4.00      | K30-40015S | K30-40020S | K30-40030S | K30-40040S | K30-40060S | K30-40080S | K30-40100S |
|             | 5.00      | K30-50015S | K30-50020S | K30-50030S | K30-50040S | K30-50060S | K30-50080S | K30-50100S |
|             | 6.00      |            |            | K30-60030S | K30-60040S | K30-60060S |            |            |
|             | 7.00      |            |            | K30-70030S | K30-70040S | K30-70060S |            |            |
| 输送杆长 150 cm | 1.50      | K30-15015M | K30-15020M | K30-15030M | K30-15040M | K30-15060M | K30-15080M | K30-15100M |
|             | 2.00      | K30-20015M | K30-20020M | K30-20030M | K30-20040M | K30-20060M | K30-20080M | K30-20100M |
|             | 3.00      | K30-30015M | K30-30020M | K30-30030M | K30-30040M | K30-30060M | K30-30080M | K30-30100M |
|             | 4.00      | K30-40015M | K30-40020M | K30-40030M | K30-40040M | K30-40060M | K30-40080M | K30-40100M |
|             | 5.00      | K30-50015M | K30-50020M | K30-50030M | K30-50040M | K30-50060M | K30-50080M | K30-50100M |
|             | 6.00      |            |            | K30-60030M | K30-60040M | K30-60060M |            |            |
|             | 7.00      |            |            | K30-70030M | K30-70040M | K30-70060M |            |            |

\*规格详见注册证

河北康誉医疗器械有限公司

网    址:http://www.courymed.com  
联系方式:0311-88882200/400-887-7986  
地    址:中国(河北)自由贸易试验区正定片区河北正定高新技术产业开发区南区崇因路15号

# 外周球囊扩张导管

## 国械注准20253030120

该产品用于颈动脉、肾动脉、股动脉、腘动脉、腘下动脉的经皮腔内血管成形术。  
该导管不适用于冠状动脉。



# 产品介绍

满足顾客需求,持续创新改进

